# **Product Data Sheet**



## **ULTRO Twin Filter Systems**

## **Modular filtration**

From the global BWT group ULTRO Twin Filter Systems provide premium filtration performance with unequalled flexibility. The BWT ULTRO Twin is perfect for medium flow point of use coffee and beverage applications. ULTRO twin systems combine a 1st stage of prefiltration followed by a 2nd stage Water + More water treatment. Prefiltration options include sediment or Fibron activated carbon filtration. Final stage options include BWT bestprotect or bestmax PREMIUM cartridges. Speak to the experienced BWT team for recommendations on the ULTRO Twin filter most suitable.

ULTRO and BWT Water + More systems carry WaterMark certification for confidence in performance and quality.

User Guides, technical support and installation schematics are available as required.



**ULTRO** Twin head assembly



ULTRO bestprotect V twin



**ULTRO bestmax PREMIUM S twin** 

#### **Features & Benefits**

- Flexible modular system media options in 2 stages to suit all applications
- Efficient Fibron prefiltration Clean, clear water to minimise flow restrictor and small orifice blockage
- One head many possibilities The BWT besthead accepts all ULTRO cartridges and the extensive Water + More range
- Compact size and diameter to fit in small spaces
- Custom twin bracket, keyholed, flush wall fit and compact
- Easy to install, use and change positive o ring screw sealing
- Efficient Fibron filter media long life high performance activated carbon block
- Custom designs available upon request

### **Specifications and operating conditions**

- Flow Rate: < 10 lpm
- Capacity:

1st stage: 30,000 litres chlorine reduction for Fibron cartridges 2nd stage: Depending on cartridge selected and water quality

- Water pressure range: 80 860 kPa Use PLV if pressure is > 860 kPa
- Water temperature range: 4 40 deg C

Dimensions for installation purposes: Standard Twin head assembly is 320mm wide - allow for extra fittings / hoses, 120mm deep

Height and weight of system will depend on cartridge selected

ULTRO cartridge and head should have 450mm height space available

### **BWT ULTRO Twin systems**

inlet options	1st stage	2nd stage	Outlet
Standard 3/8" bspm	Fibron 5m	bestprotect S,V,XL,2XL	Standard 3/8" bspm
	Fibron 5m + scale	bestmax PREMIUM S,V,M,XL,2XL	
	Fibron 1m		
	Sediment 5m		

Contact BWT for assistance in selecting the most suitable filter system